



KBN863A

**Insulated busbar 3P+N 63A prong 12 mod**

**Technical Features**

**Electric current**

Rated current 63 A

**Architecture**

Number of poles 4

**Dimensions**

Length 218.20 mm

**Voltage**

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 230 - 400 V

**Connection**

Cross-section rigid conductor 10 mm<sup>2</sup>

Connector/plug type Phase busbar with pin

**Use conditions**

Operating temperature -5 - 60 °C

**Capacity**

Number of modules 12

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes