



KBN863A

Insulated busbar 3P+N 63A prong 12 mod

Technical Features

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	4
-----------------	---

Dimensions

Length	218.20 mm
--------	-----------

Voltage

Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	230 - 400 V

Connection

Cross-section rigid conductor	10 mm <sup>2</sup>
Connector/plug type	Phase busbar with pin

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Capacity

Number of modules	12
-------------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes