



505101



Push-button insert f. hotel card switch cover 10 A, NO cont. w. 2 signal cont.

Technical Features

Electric current

| | |
|---------------------------|------|
| Switching current | 10 A |
| Momentary contact current | 10 A |

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Architecture

| | |
|---------------------------|------------|
| Control/operation element | Hotel card |
| Number of poles | 1 |

Materials

| | |
|-------------|------------------|
| Material | Metal Plastic |
| Treatment | Untreated |
| Transparent | No |

Dimensions

| | |
|------------------------------------|----------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 41 mm |
| Built-in depth | 31.20 mm |
| Built-in depth flush-mounted boxes | 44 mm |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Controls and indicators

| | |
|------------------------------|--------------------|
| Number of buttons | 0 |
| Type of push button | Single push button |
| With feedback signal contact | No |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

| | |
|--------------------|---------------------------------------------------------------------------------------------------------|
| Imprint | Without imprint |
| Lighting | Can be illuminated using neon and glow lamp unit with N-terminal For lighting and monitoring circuit |
| Switch mode | NO, with 2 separate signalling contacts |
| Type of connection | With plug-in terminals |

Suitable for

| | |
|---------------------------|--|
| K.x / Q.x / R.x / S.x/B.x | |
|---------------------------|--|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |