



676579

Soc.out. earth. pin,enhncd contact prot.,screw-in lift term.,1930/glass,p.wh.gl.

#### Technical Features

##### Voltage

Rated voltage 250 V

##### Electric current

Rated current 16 A

##### Frequency

Frequency 50 - 60 Hz

##### Materials

Colour Polar white

RAL code 9010

Surface finish Glossy

Material Duroplastic

Treatment Untreated

##### Dimensions

Height 71 mm

Width 71 mm

Depth 43.60 mm

Built-in depth flush-mounted boxes 31 mm

Built-in depth 31.40 mm

##### Installation, mounting

Mounting on Flush mounting

##### Connectivity

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

##### Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert Yes

With hinged lid No

With round protective earth pin Yes

With signal lamp No

With lock No

##### Accessories

Has labelling field No

##### Capacity

Number of modules 1

##### Safety

With enhanced contact protection Yes

Impact resistance IK IK02

Ingress Protection (IP) class IP20

##### Functions

With orientation lighting No

With function lighting No

##### Identification

With imprint No

##### Texts

Cover Central cover plate

Protection Enhanced contact protection

---

**Texts**

---

Type of connection	With screw-in lift terminals
--------------------	------------------------------

---

**Suitable for**

---

Serie 1930 / Serie Glas

---

**Sustainability**

---

Halogen free	Yes
RoHS conform	Yes

---