



WFPS32PSB

**10AX 3 Gang 2 Way Wall Switch Polished Steel Black Insert**

**Technical Features**

**Electric current**

|                   |      |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Materials**

|        |        |
|--------|--------|
| Colour | Silver |
|--------|--------|

|                |        |
|----------------|--------|
| Surface finish | Glossy |
|----------------|--------|

|          |                 |
|----------|-----------------|
| Material | Stainless steel |
|----------|-----------------|

**Identification**

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

**Dimensions**

|            |            |
|------------|------------|
| Dimensions | 86 x 86 mm |
|------------|------------|

|                |          |
|----------------|----------|
| Built-in depth | 19.10 mm |
|----------------|----------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Triple rocker |
|---------------------------|---------------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

**Texts**

|                   |  |
|-------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
|-------------------|--|

|          |  |
|----------|--|
| Lighting | Without lighting (cannot be illuminated) |
|----------|--|

|             |       |
|-------------|-------|
| Switch mode | 2-way |
|-------------|-------|

**Sustainability**

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|