



dr16f4

**Din rail board, 1 row 16M, non-transparent door, flush**

**Technical Features**

**Voltage**

Nominal voltage 415 - 415 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Flush mounting

**Power**

Maximum power loss per cabinet at  $\Delta T=20K$  12.68 W

**Equipment**

Number of rails 1

Number of rows 1

With lock No

Has neutral terminal block Yes

**Capacity**

Number of modules 16

Number of half modules terminals per rail 32

**Functions**

Has protection main switch No

With conduit inlets Yes

**Dimensions**

Height 349 mm

Width 430 mm

Depth 110 mm

Built-in height 320 mm

Built-in width 400 mm

**Cover, door**

Number of cabinet doors 1

**Dimensions**

Built-in depth 110 mm

**Cover, door**

Number of locks 0

**Dimensions**

Number of width units 16

**Cover, door**

Door/cover is transparent No

**Connection**

Number of conduit inlets 17

**Connectivity**

Mounting type Screw mounting

**Materials**

Material Steel

RAL code 9010

Colour Grey white

**Equipment**

Has earthing terminal block No

Has mounting plate No

---

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock
Glow wire test	960 °C

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes