



47803512



**Technical Features**

**Dimensions**

Dimensions	147 x 76 mm
Built-in depth flush-mounted boxes	0 mm

**Electric current**

Rated current	16 A
Switching current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Materials**

Colour	White
RAL code	7011 9010
Material	Thermoplastic
Surface finish	Matt

**Safety**

Ingress Protection (IP) class	IP55
With enhanced contact protection	No

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Equipment**

With signal lamp	No
With round protective earth pin	No
Connector/plug type socket outlet	SCHUKO
Rotated central insert	No

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Installation mode	For vertical mounting
Protection	Without enhanced contact protection
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Type of connection	With plug-in terminals

**Sustainability**

Halogen free	Yes
RoHS conform	Yes