



387500

Rot. switch, series, 1930/glass/R.classic

Technical Features

Electric current

Switching current	10 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Surface finish	Matt
----------------	------

Material	Duroplastic
----------	-------------

Identification

Assembly arrangement	Basic element
----------------------	---------------

Connectivity

Mounting type	Claw mounting
---------------	---------------

Dimensions

Dimensions	71 x 71 mm
------------	------------

Built-in depth	32 mm
----------------	-------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Short rotary handle
---------------------------	---------------------

Electric current

Rated current	10 A
---------------	------

Texts

Installation mode	With spreader claws
-------------------	---------------------

Type of connection	With screw terminals
--------------------	----------------------

Lighting	Without neon lamp
----------	-------------------

Switch mode	Series
-------------	--------