



387503

Rotary switch, series, Serie 1930/Glas/R.classic

Technical Features

Electric current

Switching current 10 AX (100W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Material Duroplastic

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Claw mounting

Dimensions

Dimensions 71 x 71 mm

Built-in depth 32 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Short rotary handle

Electric current

Rated current 10 A

Texts

Installation mode With spreader claws

Type of connection With screw terminals

Lighting Without neon lamp

Switch mode Series

Sustainability

RoHS conform Yes