



41092089

**SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,R.classic,wh**

**Technical Features**

**Electric current**

Rated current	16 A
---------------	------

**Voltage**

Rated voltage	250 V
Nominal voltage	250 - 250 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth	32 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

**Controls and indicators**

Type of lighting for the installation devices	Integrated orientation light
---	------------------------------

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	Yes
With function lighting	No

**Texts**

Imprint	Without imprint
Cover	Central cover plate

<b>Texts</b>	
Lighting	Additional benefit by combination of a socket outlet with an orientation light
Wiring	Through-wiring possible, therefore also ideal for retrofitting
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

<b>Suitable for</b>	
Berker R.x / Berker serie R.classic	

<b>Sustainability</b>	
RoHS conform	Yes