




41092045



SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,R.cl,bl.

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Black
RAL code	9005
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Number of units	1
Built-in depth	32 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Controls and indicators

Type of lighting for the installation devices	Integrated orientation light
---	------------------------------

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	Yes
With function lighting	No

Texts		
Imprint		Without imprint
Cover		Central cover plate
Lighting	Additional benefit by combination of a socket outlet with an orientation light	
Wiring	Through-wiring possible, therefore also ideal for retrofitting	
Protection		Enhanced contact protection
Type of connection		With screw-in lift terminals

Suitable for		
R.x / Serie R.classic		

Sustainability		
RoHS conform		Yes