




HCW631AR



**Load Break Switch Disconnecter h3+ P630 4P 630A FTC**

**Technical Features**

**Electric current**

Rated current	630 A
Rated short-time withstand current I <sub>cw</sub> IEC 60947	7.60 kA

**Architecture**

Number of poles	4
Control/operation element	Toggle

**Voltage**

Rated insulation voltage U <sub>i</sub>	800 V
Rated impulse withstand voltage U <sub>imp</sub>	8000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Functions**

Trip unit	Switch
-----------	--------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes