



289110



1-10 V rot. potentiometer, soft-lock, light control

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Connectivity

Dimming DALI No

Dimensions

Diameter axis 4 mm

Height 71 mm

Width 71 mm

Depth 40 mm

Electric current

Control current 50 - 50 mA

Switching current 6 A

Texts

Lighting E.g. for fluorescent lamps and LV halogen lamps

Type of connection With screw terminals

Fuse Short-circuit and overload-proof (fine-wire fuse)
With spare fuse

Suitable for

K.x / Q.x / R.x / S.x / B.x

Sustainability

REACH-SVHC free Yes

RoHS conform Yes