



289110



**1-10 V rot. potentiometer, soft-lock, light control**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Frequency**

Frequency 50 - 60 Hz

**Connectivity**

Dimming DALI No

**Dimensions**

Diameter axis 4 mm

Height 71 mm

Width 71 mm

Depth 40 mm

**Electric current**

Control current 50 - 50 mA

Switching current 6 A

**Texts**

Lighting E.g. for fluorescent lamps and LV halogen lamps

Type of connection With screw terminals

Fuse Short-circuit and overload-proof (fine-wire fuse)  
With spare fuse

**Suitable for**

K.x / Q.x / R.x / S.x / B.x

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes