



289110



1-10 V rot. potentiometer, soft-lock, light control

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Connectivity

Dimming DALI	No
--------------	----

Dimensions

Diameter axis	4 mm
Height	71 mm
Width	71 mm
Depth	40 mm

Electric current

Control current	50 - 50 mA
Switching current	6 A

Texts

Lighting	E.g. for fluorescent lamps and LV halogen lamps
Type of connection	With screw terminals
Fuse	Short-circuit and overload-proof (fine-wire fuse) With spare fuse

Suitable for

K.x / Q.x / R.x / S.x/B.x	
---------------------------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes