



17831404

Technical Features

Dimensions

Installation height	1.10 - 1.10 m
Assembling height	23.50 mm

Detection

Type of sensor	Movement detector
Detection diameter on floor	0 - 0 m
Detection angle	180 - 180
Detection angle adjustable	180 - 180 °

Materials

Colour	Aluminium
Surface finish	Matt
Treatment	Varnished
Material	Thermoplastic

Reach distance

Max. transmission range frontally	10 m
Max. transmission range sideways	6 m

Lighting

Response brightness adjustable	0 - 80 lx
--------------------------------	-----------

Settings

Response brightness adjustable	Yes
--------------------------------	-----

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------