



WMGS16BSW

**20A Intermediate Switch Brushed Steel White Insert**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Materials**

Colour Stainless steel

Surface finish Matt

Material Duroplastic  
Stainless steel

Treatment Brushed

**Identification**

Assembly arrangement Basic element with central cover plate

**Connectivity**

Mounting type Snap-on mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 60 x 25 mm

Built-in depth 13.10 mm

**Electric current**

Rated current 20 A

**Texts**

Lighting Without lighting (cannot be illuminated)

Push button No

Imprint With clear terminal markings

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes