



75144150



IP20



Touch sensor, 4-gang comf, intg bus coupling unit, KNX - R.3, glass p. white

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Power

Current consumption 12.50 mA

Dimensions

Built-in depth 12.90 mm
 Built-in depth flush-mounted boxes 16 mm
 Height 152 mm
 Width 81 mm
 Depth 23 mm

Equipment

Number of actuation points 8

Controls and indicators

With LED indication Yes

Materials

Colour Polar white
 RAL code 9010
 Material Glass
 Surface finish Glossy

Accessories

Has labelling field No

Screen

With display No

Texts

Function For switch, push-button, dimmer and shutter functions
 Blocking function for sensor surface e.g. for cleaning the glass surface
 Installation mode For vertical mounting
 Temperature Additional connection for external temperature sensor
 Integrated temperature sensor for operation as controller extension unit
 Temperature measurement via internal Temperature sensor or external communication object

Sustainability

REACH-SVHC free Yes
 RoHS conform Yes