




75144155



IP20



Touch sensor, 4-gang comf, intg bus coupling unit, KNX - R.3, glass black

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Power

Current consumption 12.50 mA

Dimensions

Built-in depth 12.90 mm
Built-in depth flush-mounted boxes 16 mm
Height 152 mm
Width 81 mm
Depth 23 mm

Equipment

Number of actuation points 8

Controls and indicators

With LED indication Yes

Materials

Colour Black
RAL code 9005
Material Glass
Surface finish Glossy

Accessories

Has labelling field No

Screen

With display No

Texts

Function For switch, push-button, dimmer and shutter functions
Blocking function for sensor surface e.g. for cleaning the glass surface
Installation mode For vertical mounting
Temperature Additional connection for external temperature sensor
Integrated temperature sensor for operation as controller extension unit
Temperature measurement via internal Temperature sensor or external communication object

Sustainability

REACH-SVHC free Yes
RoHS conform Yes