



JG220U

**IP66 20A 3P SW NEUTRAL ISOLATOR**

**Technical Features**

**Architecture**

Number of poles	4
Type of pole	3P+N

**Electric current**

Rated current	20 A
Acceptable current rating AC21	20 A
Acceptable current rating AC21 category A	20 A
Rated short-time withstand current Icw IEC 60947	0.24 kA
Acceptable current rating AC22 category A	20 A

**Voltage**

Rated operational voltage Ue	380 - 440 V
------------------------------	-------------

**Electric current**

Acceptable current rating AC23 category A	20 A
---	------

**Voltage**

Rated insulation voltage Ui	440 V
-----------------------------	-------

**Installation, mounting**

Nominal tightening torque	2 - 2 Nm
---------------------------	----------

**Dimensions**

Height	170 mm
Width	84 mm
Depth	87 mm

**Safety**

Ingress Protection (IP) class	IP66
-------------------------------	------

**Power**

Rated operational power under 400 V AC AC23	9900 W
---	--------

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

**Connection**

Cross-section rigid conductor	2.5 - 4 mm <sup>2</sup>
-------------------------------	-------------------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Sustainability**

RoHS conform	Yes
--------------	-----