



HBT250H

RCD add on P250 4P 250A I_{dn} adj

Technical Features

Electric current

Rated current	250 A
Rated residual operating current I _{dn}	30 mA 100 mA 300 mA 1000 mA 3000 mA 6000 mA

Architecture

Number of poles	4
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Voltage

Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	6000 V

Connection

Cross-section of input and output with screws, for massive conductors	35 - 185 mm ²
Cross-section of input and output with screws, for flexible conductors	35 - 150 mm ²

Sustainability

RoHS conform	Yes
--------------	-----