



510040

Surface-mtd push-button/pilot lamp E10, NO contact, surface-mtd, white glossy

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Power

Power incandescent lamp	2 - 2 W
-------------------------	---------

Materials

Colour	White
RAL code	1013
Surface finish	Glossy
Material	Duroplastic
Treatment	Untreated

Dimensions

Height	61.20 mm
Width	61 mm
Depth	41.50 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Lighting	For lighting and monitoring circuit
Imprint	Without imprint

Sustainability

RoHS conform	Yes
--------------	-----