



WRPS22WBSB

10AX 2 Gang 2 Way Wall Switch Wide Rocker Brushed Steel Black Insert

Technical Features

Electric current

Switching current	10 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Stainless steel
Surface finish	Matt
Material	Stainless steel
Treatment	Brushed

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	2
-------------------	---

Dimensions

Dimensions	86 x 86 mm
Built-in depth	11.20 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Double rocker
---------------------------	---------------

Electric current

Rated current	10 A
---------------	------

Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes