



EU300

control relay triphased phase 400V

Technical Features

Capacity

Number of modules	2
-------------------	---

Use conditions

Operating temperature	-20 - 55 °C
Storage/transport temperature	-40 - 70 °C

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Dimensions

Height	85 mm
Depth	64 mm

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Power

Total power loss under IN	4 W
---------------------------	-----

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Electric current

Acceptable current rating AC1	8 A
-------------------------------	-----

Installation, mounting

Mounting on	DIN rail
-------------	----------