



LNH0080M

**HRC LV fuse NH000 gG AC500V 80A double indicator with live gripping-lugs**

**Technical Features**

**Architecture**

|       |    |
|-------|----|
| Curve | gG |
|-------|----|

**Fuse**

|                      |       |
|----------------------|-------|
| Fuse size            | NH000 |
| Fuse characteristics | gG    |

**Voltage**

|                              |             |
|------------------------------|-------------|
| Type voltage supply          | AC/DC       |
| Rated operational voltage Ue | 500 - 500 V |
| Rated voltage at AC 50 Hz    | 500 - 500 V |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 80 A |
|---------------|------|

**Use conditions**

|           |    |
|-----------|----|
| Insulated | No |
|-----------|----|

**Main electrical attributes**

|   |        |
|---|--------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 120 kA |
|---|--------|

**Power**

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 6.50 W |
|---------------------------|--------|

**Dimensions**

|        |          |
|--------|----------|
| Height | 58.50 mm |
| Width  | 21 mm    |
| Depth  | 79 mm    |

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |