




85121200



Relay insert, electronics

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Controls and indicators

Applicable with movement sensor	Yes
---------------------------------	-----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Power consumption standby	0.30 W
230 V incandescent and halogen lamp	2300 W
Fluorescent lamps in duo circuit	1000 W

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Dimensions

Built-in depth	32 mm
----------------	-------

Texts

Extension unit input	With extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit
Installation mode	With spreader claws
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes