



85121200



Relay insert, electronics

Technical Features

Voltage

Operating voltage 230 - 230 V

Controls and indicators

Applicable with movement sensor Yes

Frequency

Frequency 50 - 60 Hz

Power

Power consumption standby 0.30 W

230 V incandescent and halogen lamp 2300 W

Fluorescent lamps in duo circuit 1000 W

Use conditions

Operating temperature -5 - 45 °C

Dimensions

Built-in depth 32 mm

Texts

Extension unit input With extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit

Installation mode With spreader claws

Type of connection With screw terminals

Sustainability

REACH-SVHC free Yes

RoHS conform Yes