



85121200



**Relay insert, electronics**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Controls and indicators**

Applicable with movement sensor Yes

**Frequency**

Frequency 50 - 60 Hz

**Power**

Power consumption standby 0.30 W

230 V incandescent and halogen lamp 2300 W

Fluorescent lamps in duo circuit 1000 W

**Use conditions**

Operating temperature -5 - 45 °C

**Dimensions**

Built-in depth 32 mm

**Texts**

Extension unit input With extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit

Installation mode With spreader claws

Type of connection With screw terminals

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes