



HWX013H

**Spring charging motor 100-130V AC 50/60Hz HW2/4 (MO)**

**Technical Features**

**Electric current**

Rated current	2.30 A
---------------	--------

**Voltage**

Type voltage supply	AC
Rated insulation voltage $U_i$	450 V
Rated impulse withstand voltage $U_{imp}$	6000 V
Command voltage AC	100 - 130 V

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Functions**

With auto reset function	No
--------------------------	----

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes