



75663592



### B.IQ push-button 3gang thermostat, display, KNX - B.IQ, glass black

#### Technical Features

##### Installation, mounting

Mounting on Flush mounting

##### Use conditions

Operating temperature -5 - 45 °C

##### Functions

With room temperature controller Yes

##### Dimensions

Height 119.60 mm

Width 88.50 mm

Depth 16.65 mm

##### Equipment

Number of actuation points 8

##### Controls and indicators

With LED indication Yes

##### Materials

Colour Black

RAL code 9005

Material Glass

Surface finish Glossy

##### Accessories

Has labelling field No

##### Screen

With display Yes

##### Texts

Function For switch, push-button, dimmer, blind and thermostat functions  
With valve protection function  
Button help function can be activated

Operating mode Controller operating modes: comfort, standby, night and frost/heat protection mode

Protection With dismantling protection

Temperature Temperature measurement via internal Temperature sensor and/or external communication object (weighting ratio parameterisable)  
Provision of the internal temperature value via communication object

##### Sustainability

REACH-SVHC free Yes

RoHS conform Yes