



75663593



**B.IQ push-b. 3gang thermostat, display, KNX - B.IQ, stainl. steel metal brushed**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Functions**

With room temperature controller Yes

**Dimensions**

Height 119.60 mm

Width 88.50 mm

Depth 16.65 mm

**Equipment**

Number of actuation points 8

**Controls and indicators**

With LED indication Yes

**Materials**

Colour Stainless steel

RAL code 9022

Material Metal  
Stainless steel

Surface finish Matt

**Accessories**

Has labelling field No

**Screen**

With display Yes

**Texts**

Function For switch, push-button, dimmer, blind and thermostat functions  
With valve protection function  
Button help function can be activated

Operating mode Controller operating modes: comfort, standby, night and frost/heat  
protection mode

Protection With dismantling protection

Temperature Temperature measurement via internal Temperature sensor and/or  
external communication object (weighting ratio parameterisable)  
Provision of the internal temperature value via communication object

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes