



75663593



## B.IQ push-b. 3gang thermostat, display, KNX - B.IQ, stainl. steel metal brushed

### Technical Features

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

#### Functions

With room temperature controller	Yes
----------------------------------	-----

#### Dimensions

Height	119.60 mm
Width	88.50 mm
Depth	16.65 mm

#### Equipment

Number of actuation points	8
----------------------------	---

#### Controls and indicators

With LED indication	Yes
---------------------	-----

#### Materials

Colour	Stainless steel
RAL code	9022
Material	Metal Stainless steel
Surface finish	Matt

#### Accessories

Has labelling field	No
---------------------	----

#### Screen

With display	Yes
--------------	-----

#### Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function Button help function can be activated
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Protection	With dismantling protection
Temperature	Temperature measurement via internal Temperature sensor and/or external communication object (weighting ratio parameterisable) Provision of the internal temperature value via communication object

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes