



75663594



B.IQ push-button 3gang thermostat, display, KNX - B.IQ, al., al. anodised

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Dimensions

Height 119.60 mm

Width 88.50 mm

Depth 16.65 mm

Equipment

Number of actuation points 8

Controls and indicators

With LED indication Yes

Materials

Colour Aluminium

RAL code 9006

Material Aluminium

Surface finish Matt

Accessories

Has labelling field No

Screen

With display Yes

Texts

Function For switch, push-button, dimmer, blind and thermostat functions
With valve protection function
Button help function can be activated

Operating mode Controller operating modes: comfort, standby, night and frost/heat
protection mode

Protection With dismantling protection

Temperature Temperature measurement via internal Temperature sensor and/or
external communication object (weighting ratio parameterisable)
Provision of the internal temperature value via communication object

Sustainability

REACH-SVHC free Yes