



MZ201

Auxiliary contact 1C+1O 6A 240V AC

Technical Features

Electric current

Rated current	6 A
---------------	-----

Connectivity

Type of connection	Screw terminal
Mounting type	Click mounting

Capacity

Number of modules	0.50
-------------------	------

Connection

Type of contacts	1NC+1NO
Cross-section flexible conductor	6 mm ²
Cross-section rigid conductor	10 mm ²

Voltage

Rated insulation voltage Ui	4000 V
Type voltage supply	AC

Endurance

Number of mechanical operations	12000
---------------------------------	-------

Use conditions

Operating temperature	-25 - 60 °C
-----------------------	-------------

Endurance

Electric endurance in number of cycles	6000
--	------

Use conditions

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

Power

Total power loss under IN	0.10 W
---------------------------	--------

Dimensions

Height	80 mm
Width	9.50 mm
Depth	40 mm

Equipment

Number of INV contacts	0
Number of NC contacts	1

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

