Product Datasheet
MZ202

MZ202

Alarm contact 1C+1O 6A 240V AC

Technical Features

Electric current	
Rated current	6 A
Connectivity	
Type of connection	Screw terminal
Mounting type	Click mounting
Capacity	
Number of modules	0.50
Connection	
Type of contacts	1NC+1NO
Cross-section flexible conductor	6 mm^2
Cross-section rigid conductor	10 mm^2
Voltage	
Rated insulation voltage Ui	4000 V
Type voltage supply	AC
Endurance	
Number of mechanical operations	12000
Use conditions	
Operating temperature	-25 - 60 °C
Endurance	
Electric endurance in number of cycles	6000
Use conditions	
Storage/transport temperature	-40 - 80 °C
Power	
Total power loss under IN	0.20 W
Dimensions	
Width	9 mm
Depth	68 mm
Equipment	
Number of INV contacts	0
Number of NC contacts	1
Sustainability	
RoHS conform	Yes

Illustrations | Drawings