



MZ202

**Alarm contact 1C+1O 6A 240V AC**

**Technical Features**

**Electric current**

Rated current	6 A
---------------	-----

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Capacity**

Number of modules	0.50
-------------------	------

**Connection**

Type of contacts	1NC+1NO
Cross-section flexible conductor	6 mm <sup>2</sup>
Cross-section rigid conductor	10 mm <sup>2</sup>

**Voltage**

Rated insulation voltage Ui	4000 V
Type voltage supply	AC

**Endurance**

Number of mechanical operations	12000
---------------------------------	-------

**Use conditions**

Operating temperature	-25 - 60 °C
-----------------------	-------------

**Endurance**

Electric endurance in number of cycles	6000
--	------

**Use conditions**

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

**Power**

Total power loss under IN	0.20 W
---------------------------	--------

**Dimensions**

Width	9 mm
Depth	68 mm

**Equipment**

Number of INV contacts	0
Number of NC contacts	1

**Sustainability**

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

