



MZ203

**Shunt trip 230-415V AC 110-130V DC**

**Technical Features**

**Power**

Inrush power absorbed	15 VA
-----------------------	-------

**Use conditions**

Operating temperature	-25 - 60 °C
-----------------------	-------------

**Voltage**

Command voltage AC	230 - 415 V
Command voltage DC	110 - 130 V
Type voltage supply	AC/DC
Rated insulation voltage $U_i$	4000 V
Rated operational voltage $U_e$	230 - 415 V
Rated operational voltage in DC	110 - 130 V

**Dimensions**

Height	83 mm
Width	18 mm
Depth	68 mm

**Capacity**

Number of modules	1
-------------------	---

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

