




MZ203

Shunt trip 230-415V AC 110-130V DC

Technical Features

Power

Inrush power absorbed	15 VA
-----------------------	-------

Use conditions

Operating temperature	-25 - 60 °C
-----------------------	-------------

Voltage

Command voltage AC	230 - 415 V
Command voltage DC	110 - 130 V
Type voltage supply	AC/DC
Rated insulation voltage U_i	4000 V
Rated operational voltage U_e	230 - 415 V
Rated operational voltage in DC	110 - 130 V

Dimensions

Height	83 mm
Width	18 mm
Depth	68 mm

Capacity

Number of modules	1
-------------------	---

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

