



MZ204

Shunt trip 24-48V AC 12-48V DC

Technical Features

Power

|                       |       |
|-----------------------|-------|
| Inrush power absorbed | 27 VA |
|-----------------------|-------|

Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25 - 60 °C |
|-----------------------|-------------|

Voltage

|                                 |           |
|---------------------------------|-----------|
| Command voltage AC              | 24 - 48 V |
| Command voltage DC              | 12 - 48 V |
| Type voltage supply             | AC/DC     |
| Rated insulation voltage $U_i$  | 4000 V    |
| Rated operational voltage $U_e$ | 24 - 48 V |
| Rated operational voltage in DC | 12 - 48 V |

Dimensions

|        |       |
|--------|-------|
| Height | 83 mm |
| Width  | 18 mm |
| Depth  | 68 mm |

Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Illustrations | Drawings

