



MZ204

**Shunt trip 24-48V AC 12-48V DC**

**Technical Features**

**Power**

Inrush power absorbed 27 VA

**Use conditions**

Operating temperature -25 - 60 °C

**Voltage**

Command voltage AC 24 - 48 V

Command voltage DC 12 - 48 V

Type voltage supply AC/DC

Rated insulation voltage  $U_i$  4000 V

Rated operational voltage  $U_e$  24 - 48 V

Rated operational voltage in DC 12 - 48 V

**Dimensions**

Height 83 mm

Width 18 mm

Depth 68 mm

**Capacity**

Number of modules 1

**Sustainability**

RoHS conform Yes

**Illustrations | Drawings**

