



MZ204

**Shunt trip 24-48V AC 12-48V DC**

**Technical Features**

**Power**

Inrush power absorbed	27 VA
-----------------------	-------

**Use conditions**

Operating temperature	-25 - 60 °C
-----------------------	-------------

**Voltage**

Command voltage AC	24 - 48 V
Command voltage DC	12 - 48 V
Type voltage supply	AC/DC
Rated insulation voltage $U_i$	4000 V
Rated operational voltage $U_e$	24 - 48 V
Rated operational voltage in DC	12 - 48 V

**Dimensions**

Height	83 mm
Width	18 mm
Depth	68 mm

**Capacity**

Number of modules	1
-------------------	---

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

