



85121100



Switch insert 1gang, electronics

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Controls and indicators

Applicable with movement sensor	Yes
---------------------------------	-----

Lighting

LED lamp power	250 W
----------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

leading edge dimmer	Yes
trailing edge dimmer	Yes

Lighting

Dimmable 230 V LED lamp	5 - 70 W
-------------------------	----------

Power

Power consumption standby	0.30 W
---------------------------	--------

Capacity

Number of modules	0
-------------------	---

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Dimensions

Built-in depth	32 mm
----------------	-------

Texts

Dimming principle	Automatic setting of load-dependent switching principle (autodetect process)
Extension unit input	With extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals