



303212

On/off switch 2pole 16 AX, light control

Technical Features

Electric current

Switching current 16 AX (200W LED (SBL))

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Surface finish Matt

Material Metal
Plastic

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 71 x 71 mm

Built-in depth 32 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Impact resistance IK IK07

Usable in higher IP class IP44 in combination with sealing set

Electric current

Rated current 16 A

Texts

Installation mode With spreader claws

Type of connection With screw terminals

Lighting For lighting and monitoring circuit

Push button No

Sustainability

RoHS conform Yes