



47703532

**SCHUKO soc.out. 2gang vert. hinged cover surface-mtd, W.1, p.white matt, plastic**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	147 mm
Width	76 mm
Depth	65 mm
Built-in depth flush-mounted boxes	0 mm
Height of P-touch band for labelling field	12 mm

**Connection**

Connector/plug type	Plug-in terminal
Conductor cross-section	1.0 - 2.5 mm <sup>2</sup>

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Connectivity**

Type of connection	Plug-in connection
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	Yes
---------------------	-----

**Cover, door**

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

**Capacity**

Number of modules	2
-------------------	---

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP55

---

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Texts**

Wiring	Inserts wired-through
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Labelling	With labelling field

**Sustainability**

Halogen free	Yes
RoHS conform	Yes