



MZ205

**Under voltage release 48V DC**

**Technical Features**

**Power**

Inrush power absorbed	2.40 VA
-----------------------	---------

**Use conditions**

Operating temperature	-25 - 60 °C
-----------------------	-------------

**Voltage**

Command voltage AC	0 - 0 V
Command voltage DC	48 - 48 V
Rated insulation voltage $U_i$	4000 V
Type voltage supply	DC

**Functions**

Delayed	No
---------	----

**Dimensions**

Width	17.50 mm
Depth	68 mm

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

