



MZ205

Under voltage release 48V DC

Technical Features

Power

Inrush power absorbed 2.40 VA

Use conditions

Operating temperature -25 - 60 °C

Voltage

Command voltage AC 0 - 0 V

Command voltage DC 48 - 48 V

Rated insulation voltage U_i 4000 V

Type voltage supply DC

Functions

Delayed No

Dimensions

Width 17.50 mm

Depth 68 mm

Sustainability

RoHS conform Yes

Illustrations | Drawings

