



MZ205

Under voltage release 48V DC

Technical Features

Power

Inrush power absorbed	2.40 VA
-----------------------	---------

Use conditions

Operating temperature	-25 - 60 °C
-----------------------	-------------

Voltage

Command voltage AC	0 - 0 V
Command voltage DC	48 - 48 V
Rated insulation voltage U_i	4000 V
Type voltage supply	DC

Functions

Delayed	No
---------	----

Dimensions

Width	17.50 mm
Depth	68 mm

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

