



MZ206

Under voltage release 230V AC

Technical Features

Power

Inrush power absorbed	3.50 VA
Total power loss under I _N	2 W

Use conditions

Operating temperature	-25 - 60 °C
-----------------------	-------------

Voltage

Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V
Rated insulation voltage U _i	4000 V
Type voltage supply	AC

Functions

Delayed	No
---------	----

Dimensions

Width	17.50 mm
Depth	68 mm

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

