



936712568



Push-button, NO contact, screw terms, Integro - Design Flow/Pure, chr m, lacq

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Single rocker
Number of poles	1

**Materials**

Colour	Chrome
Surface finish	Matt
Material	Thermoplastic
Treatment	Chrome plated Varnished
Transparent	No

**Dimensions**

Height	55.50 mm
Width	55.50 mm
Depth	25 mm
Built-in depth	10 mm
Built-in depth flush-mounted boxes	13 mm

**Controls and indicators**

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Safety**

Ingress Protection (IP) class	IP44
-------------------------------	------

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Imprint	Without imprint
Type of connection	With screw terminals

**Suitable for**

integro	
---------	--

**Sustainability**

RoHS conform	Yes
--------------	-----