



JK208BDFG

JK208 80 Module Side DIN Box Glazed

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	250 A
---------------	-------

Equipment

Number of rows	5
With lock	Yes
Has neutral terminal block	Yes

Capacity

Number of modules	80
-------------------	----

Dimensions

Height	950 mm
Width	465 mm
Depth	165.50 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Number of width units	80
-----------------------	----

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock Quarter turn lock

Sustainability

RoHS conform	Yes
--------------	-----